

DynoWare

Type 2825A...

Software for Data Acquisition and Evaluation

Kistler DynoWare is a universal and easy to use software, which is particularly suitable for force measurements with dynamometers or single and multi-component force sensors.

- Simple operation
- Configuration and control of Kistler measuring instruments via USB, RS-232C or IEEE-488
- Useful signal evaluation and calculation functions
- Simultaneous recording of up to 28 measuring channels
- Realtime visualization of measured curves
- The software is ideal for the acquisition and evaluation of physical measurands

Description

For signal analysis, DynoWare offers the technician realtime visualization of the measured curves together with useful calculation and graphics functions. Apart from simple configuration of the most important measuring instruments, this software supports individual documentation of the measurement, along with storage of configuration data and measured data. The signal evaluation also enables compensation of undesirable signal drift due, for example, to undue influence of temperature.

DynoWare supports several A/D cards (PCI/PCMCIA) as well as USB 2.0 of DAQ-System Type 5697A.

Application

DynoWare is the data acquisition software of choice for cutting force measurement. It supports both stationary and rotary measuring systems from Kistler.

However, DynoWare can also be used for any reaction force measurements or crash measurements with Kistler multicomponent dynamometers. At the same time, the measured data from signal amplifiers of other manufacturers can also be measured and evaluated.



Technical Data

Data Acquisition Cards Supported

Type 2855A4, PCIM-DAS 1602/16

PC bus: PCI

Number of measuring channels: 8, analog, differential

Resolution: 16 Bit

Measuring range: $\pm 1,25$ V; $\pm 2,5$ V; ± 5 V; ± 10 V

Sampling rate: 1 measuring channel active: 100 kS/s

8 measuring channels active: 12,5 kS/s

Type 2855A5, PC-CARD-DAS 16/16¹⁾

PC bus: PCMCIA, PC-CARD

Number of measuring channels: 8, analog, differential

Resolution: 16 Bit

Measuring range: $\pm 1,25$ V; $\pm 2,5$ V; ± 5 V; ± 10 V

Sampling rate: 1 measuring channel active: 100 kS/s

8 measuring channels active: 12,5 kS/s

Type 5697A: USB DAQ-System

Connection: UBS 2.0

Number of measuring channels: 28²⁾, analog, single-ended

Resolution: 16 Bit

Measuring range: $\pm 0,1$ V, $\pm 0,2$ V, $\pm 0,5$ V, ± 1 V, ± 2 V, ± 5 V, ± 10 V

Sampling rate: 1 Channel active: 1 MS/s

8 Channels active: 125 kS/s

16 Channels active: 62,5 kS/s

¹⁾ Not supported on Windows Vista and Windows 7.

²⁾ DynoWare Type 2825A as well as Update Type 2825E allow to control one charge amplifier only. DAQ-System Type 5697 is capable to acquire 28 channels maximum.

Measuring Instrument Control and Configuration via Communication Interfaces

RS-232C
5011Bx2, 5015A..., 5017..., 5018A..., 5019..., 5070A..., 5080A..., 5223..., 5237..., 5238...

IEEE-488
5011Bx1, 5015Ax1xx, 5070Axxxx1

USB 2.0
5018A..., 5080A...

Triggering

Analog, digital and by Keyboard

Digital Signal Evaluation

- Within a measuring window
 - Averaging
 - Minimum and maximum values
 - Integral
 - Determining the signal frequency
- Signal smoothing/filtering
 - Moving mean value
 - Moving median value
 - Filters: High pass, low pass, band pass and band stop
- Compensation of signal drift

Graphics Functions

- Measured data represented on one or more graphs
- Display as y(t) and y(x) graphs
- Display of numeric values
- Cursor function
- Zoom function

Calculation Functions

- Multi-component force-moment calculation
- Calculation of radial and tangential forces with rotating cutting force dynamometer Type 9123.../24...
- Mathematical functions

Tools

- Voltmeter function
- Oscilloscope function


Documentation of the Measurement

- Each measurement can be individually documented.
- Storage of measurement and configuration data with or without remarks
- Export of measured data and ASCII format (.txt) or (.csv) for Excel, DIAdem, LabVIEW, Matlab, etc.

Printer




Printing of test records and configuration data is supported by Windows

Example of a Test Record



2825A_000-371e-03.11



Cable Concept for DynoWare Type 2825A... with DAQ-System Typ 5697A

Signal Conditioner	Measuring Signal Connecting Cable	A/D Acquisition Card
Type 5017... 5019... 5070... 5080... ³⁾ 5223... 5237... 5238...	<p style="text-align: center;">Type 1700A111A2</p> <p style="text-align: center;">D-Sub pos. 15 pole D-Sub neg. 15 pole</p>  <p style="text-align: center;">2m</p>	<p style="text-align: center;">Type 5697A</p>  <p style="text-align: center;">D-Sub pos. 15 pole</p>
Type 5011... 5015... 5017... 5018... 5019... 5223... 5237... 5238... other products	<p style="text-align: center;">Type 1700A113A2</p> <p style="text-align: center;">8x BNC pos. D-Sub neg. 15 pole</p>  <p style="text-align: center;">2 m</p>	







³⁾ Cable Type 1700A111A2 can be used in addition with DAQ-System Type 5697A, regardless of summed or output signals being acquired.

2825A_000-371e-03.11

Interface Cables

Signal Conditioner	RS-232C Interface Cable (Null Modem)
Type 5011Bx2 5017... 5019... 5223...	<p style="text-align: center;">Type 1475A3</p> <p>D-Sub pos. 25 pole D-Sub neg. 9 pole</p>  <p style="text-align: center;">3 m</p>
Type 5015... 5018... 5070... 5080... 5237... 5238...	<p style="text-align: center;">Type 1200A27</p> <p>D-Sub pos. 9 pole D-Sub neg. 9 pole</p>  <p style="text-align: center;">5 m</p>

Typical Measuring Chain with DAQ-System Type 5697A1

					
Dynamometer	Connecting cable, high resistant	Charge Amplifier	Connecting cable	DAQ-System	Notebook (customer) with DynoWare
Type 9129AA	Type 1677A5	Type 5070A	Type 1700A111A2 Type 1200A27	Type 5697A1	

2825A_000-371e-03..11

Requirements for the PC

- Operating System: Windows® NT4.0 (SP4), 2000, XP, Vista, Windows® 7 (32-bit/64-bit versions)
- Pentium PC 500 MHz or higher
- Hard disc: 100 MB free space for data storage and software installation
- Memory: at least 512 MB RAM
- Super VGA monitor, screen resolution set to at least 800x600
- Vacant port (PCI or PC-CARD) for data acquisition board Type 2855A4/2855A5
- USB 2.0 port for DAQ-System Type 5697A
- USB port for USB/RS-232C converter (Type 2867)
- Parallel interface Centronics (LPT1) or USB for license key
- CD-ROM drive
- A color printer is recommended for creating hard copies of graphs
- Acrobat® Reader® for reading the PDF Instruction Manual

Optional Accessories

Type

- | | |
|-------------------------|---------------------------|
| • Data acquisition card | 2855A4, PCIM-DAS 1602/16 |
| • Data acquisition card | 2855A5, PC-CARD-DAS 16/16 |
| • DAQ system, USB | 5697A... |
| • Connecting cable | 1500B15 |
| • Connecting cable | 1500A67 |
| • Connecting cable | 1700A111A2 |
| • Connecting cable | 1500B69 |
| • Connecting cable | 1700A113A2 |
| • Interface cable | 1200A27 |
| • Interface cable | 1475A3 |
| • USB/RS-232C converter | 2867 |

Ordering Key

Scope of Delivery Including Accessories

Type

DynoWare Complete Version

2825A-02-1

- Runtime license key for parallel interface
- DynoWare software on CD-ROM
- Instruction manual

DynoWare Complete Version

2825A-02-2

- Runtime license key for USB interface (HASP)
- DynoWare software on CD-ROM
- Instruction manual

DynoWare Update Version

2825E-02-0

- DynoWare software on CD-ROM
- Instruction manual

DynoWare Demo Version

2825D-02-0

- DynoWare software on CD-ROM

DAQ-System for DynoWare

5697A1

Complete version

- HASP license key
- DynoWare software on CD-ROM, Type 2825A
- USB 2.0 DAQ-box
- USB cable, length 1,8 m
- Universal AC/DC adapter 100 ... 240 V
- Instruction manual

DAQ-System for DynoWare

5697A2

Update version

- DynoWare software on CD-ROM, Type 2825E
- USB 2.0 DAQ-box
- USB cable, length 1,8 m
- Universal AC/DC adapter 100 ... 240 V
- Instruction manual

2825A_000-371e-03.11

Windows® is a registered trade mark of Microsoft Corporation.
 Adobe® Reader® is a registered trade mark of Adobe.